

VITRON IG-6 – discover the Original


Our glass IG-6 features excellent transmittance and low thermal change in refractive index and dispersion.

IG-6 is ideal for applications in combination with other IR material for color corrected designs and infrared optical systems without thermal defocusing in the 2-12 μm spectrum.

Molding, classical polishing or Single-Point-Diamond-Machining permits the production of optical components with flat, spherical and/or aspherical shaped surfaces for the Infra-Red and Optoelectronics industries.

Antireflection coatings further improve transmission by reducing the reflection at the air-glass interfaces.

VITRON currently produces 5 different types of Chalcogenide Glass that are applicable to optics and optoelectronics system design.




Typical delivery in form of blanks:

- ∅ 5 – 150 mm
- 5 – 100 mm
- ct 0.8 – 150 mm

Index of Refraction (@ 20°C)

| λ [μm] | n(λ) |
|--------|--------|
| 1.00 | 2.9314 |
| 1.50 | 2.8462 |
| 2.00 | 2.8200 |
| 3.00 | 2.8017 |
| 4.00 | 2.7948 |
| 5.00 | 2.7910 |
| 6.00 | 2.7882 |
| 7.00 | 2.7857 |
| 8.00 | 2.7833 |
| 9.00 | 2.7808 |
| 10.00 | 2.7781 |
| 11.00 | 2.7753 |
| 12.00 | 2.7721 |



Sellmeier-Coefficients (@ 20°C)

| | |
|----------------------|---------|
| A | 4.1100 |
| B₁ | 3.6697 |
| C₁ | 0.4264 |
| B₂ | 2.3590 |
| C₂ | 59.5551 |

$$n^2(\lambda) = A + \frac{B_1 \lambda^2}{\lambda^2 - C_1^2} + \frac{B_2 \lambda^2}{\lambda^2 - C_2^2}$$

Dispersion (@ 20°C)

| λ [μm] | v _λ |
|--------|----------------|
| 4.00 | 168 |
| 10.00 | 159 |

$$v_4 = \frac{n_4 - 1}{n_3 - n_5}$$

$$v_{10} = \frac{n_{10} - 1}{n_8 - n_{12}}$$


Thermo-Optical Coefficient (@ 20°C)

| λ [μm] | dn/dT [x10 ⁻⁶ /K] |
|--------|------------------------------|
| 3.40 | 35.5 |
| 10.60 | 32.2 |

VITRON IG-6 – discover the Original

Transmission

| λ [μm] | $T(\lambda)$ [%] |
|-----------------------------|------------------|
| 1.00 | 53.2 |
| 1.50 | 59.5 |
| 2.00 | 61.2 |
| 3.00 | 60.3 |
| 4.00 | 61.4 |
| 5.00 | 61.9 |
| 6.00 | 62.2 |
| 7.00 | 62.9 |
| 8.00 | 63.5 |
| 9.00 | 62.7 |
| 10.00 | 63.4 |
| 11.00 | 62.8 |
| 12.00 | 61.9 |
| 13.00 | 49.1 |
| 14.00 | 31.5 |



Material Properties

| | $\text{As}_{40}\text{Se}_{60}$ | |
|----------------------------------|--------------------------------|--|
| Composition | | |
| Density | 4.63 | $\text{g}\cdot\text{cm}^{-3}$ |
| Thermal Expansion (20°C – 100°C) | 20.7 | $\times 10^{-6} \text{K}^{-1}$ |
| Specific Heat Capacity | 0.36 | $\text{J}\cdot\text{g}^{-1}\cdot\text{K}^{-1}$ |
| Thermal Conductivity | 0.24 | $\text{W}\cdot\text{m}^{-1}\cdot\text{K}^{-1}$ |
| Transition Temperature | 185 | °C |
| Softening Point | 236 | °C |
| Young's Modulus | 18.3 | GPa |
| Modulus of Rupture | 17 | MPa |
| Shear Modulus | 8 | GPa |
| Hardness (Knoop) | 1.04 | GPa |

Chemical Properties

The VITRON chalcogenid glasses are insoluble in water. Under normal circumstances, no reactions are observed between glass and organic solvents.

Typical Forms of Supply

Our chalcogenid glasses are fine-annealed with 3.75 K/h. Variability of the index of refraction: between charges $\leq 10^{-3}$
within a charge $\leq 10^{-4}$

Semi-finished: Boules, Blanks in disk and rectangular shapes, Rods
Other shapes by customer request

Optical components: Windows, Lenses, Prisms and other optical parts according to customer specification
AR/AR coatings on customer request

VITRON
Spezialwerkstoffe GmbH
Maau
Am Naßtal 5
D-07751 Jena

Phone: +49-(0)3641-2 88 1-30
Fax: +49-(0)3641-2 88 1-55
Email: kontakt@vitron.de
Internet: www.vitron.de

VITRON
Your Material Specialist